

NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT PART NO.: UPS003024024015
(Uninterruptible Power Supply)

ACCESSORIES

Load Sense Module Panduit part number UPS003LSM

UPS GENERAL SPECIFICATIONS

Input Power

- Voltage: 24.0 to 28.0 VDC
- Power: Fast Charge: 53 W Max.
- Medium Charge: 37 W Max.
- Slow Charge: 20 W Max.
- Current: 3.6 A Max.
- Protection: Over-voltage shut down at 32VDC.
- Maximum overvoltage is: +60VDC at 25°C ambient
- Reverse voltage maximum is: -60VDC at 25°C ambient

Output Power

- Voltage: Input present: 500 mV drop at 35 W load
- Input not present: 21.0 to 23.0 VDC
- Current: 1.6 A Max.
- Short circuit rating: 3.6 to 4.6 A


Environmental

- Operating Temperature: -40°C to +60°C.
- Storage (non-operational) Temperature: -40°C to +70°C.
- Humidity: 0 to 95% RH, noncondensing
- Operational Vibration: 2G at 10 to 500 Hz
- Operational Shock: 20G (11ms 3 bumps / direction, 18 bumps in total)

Weight: 2177 gr. / 4.8 lbs.

Numbers shown in parentheses [] are inches.

F:\wrkgrp\rvusers\ENGR DOCS\CUSTOMER DRAWINGS\FG27232B01_01.doc

							UPS003024024015 (UNINTERRUPTIBLE POWER SUPPLY)					
							CUSTOMER DRAWING					
							ITEM REVISION NAME: FG27232B01_01				PANDUIT	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---					
							 THIRD ANGLE PROJECTION				MATERIAL: -----	
01	2-11-14	BLR	SILD	ALP	UPD GRAPHIC AND SPECS	4628					DRAWING NUMBER: FG27232B01	
00	10/11/13	BLR	SILD	ALP	RELEASED	4606						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: BLR	DATE: 10-11-13	CHK SILD	SCALE NONE	SHT 1 OF 1	SIZE B