




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
V1B1B1A0A24AJA0	6.6kg (14.59lbs)


NOTES:  
1. IDENTIFICATION: VERTICAL, (24) NEMA 5-15R, BASIC  
120V / 15A / SINGLE-PHASE PDU

PART NO. V1B1B1A0A24AJA0      COLOR BLACK


- 2. ACCESSORY COMPONENTS:  
(1) QUICK-START GUIDE
- 3. PRIMARY DIMENSIONS ARE IN MILLIMETERS,  
SECONDARY DIMENSIONS IN [INCHES]
- 4. ROHS COMPLIANT
- 5. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR  
A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE  
WITH THIS PART
- 6. MAXIMUM AVAILABLE INPUT POWER = 1.8 kW
- 7. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE  
NATIONAL, STATE, AND LOCAL CODES



REAR VIEW




FRONT VIEW



SIDE VIEW



PLUG  
15 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-15P



TWENTY FOUR (24)  
RECEPTACLES  
15 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-15R

00A	09-19-14	SAT	MRWA	EDM	RELEASED TO PRODUCTION	12V092CY
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
BASIC PDU (24) 5-15R CUSTOMER DRAWING			
ITEM REVISION NAME		12V092CY/00	
DATASET FILE NAME		12V092CY_DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES	METRIC - MILLIMETER	ANGLE	
X.X +/- 0.03	X. +/- 0.8	+/- 1°	
X.XX +/- 0.018	X.X +/- 0.46		
X.XXX +/- 0.007	X.XX +/- 0.18		
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY SAT		12V092CY_DC	
DATE 09/15/14		SHT 1 OF 1	
CHK MRWA		SIZE B	
SCALE NTS			