


PANDUIT P/N	WEIGHT
GM-A0926BL	5 kg (11 lb)

NOTES:  
1. IDENTIFICATION: GATEWAY MONITORED ZERO-RU INLINE METER, (1) 30A IEC60309, 208V / 30A / SINGLE-PHASE PDU


PART NO.                      COLOR  
GM-A0926BL                  BLACK RAL 9005

2. ACCESSORY COMPONENTS:
- (4) M6 x 12mm MOUNTING SCREWS
  - (4) M6 x 12mm MOUNTING SCREWS
  - (4) M6 NUT (CAGED)
  - (1) M5 NUT (NYLON INSERT)
  - (1) M5 LOCK WASHER


3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]  
4. INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED VIA ON UNIT DISPLAY OR REMOTELY.  
5. RoHS COMPLIANT.  
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.  
7. MAXIMUM AVAILABLE INPUT POWER = 5.0 kW  
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




TOP VIEW





SIDE VIEW



FRONT VIEW



00A	09/10/14	DACU	JPHI		RELEASED TO PRODUCTION	AA0926CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATUTE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.			SIGN	
			DATE	
			PRINT	
TITLE SmartZone Gateway-Enabled Zero-RU Inline Meter PN: GM-A0926BL CUSTOMER DRAWING				
ITEM REVISION NAME AA0926CP/00.PRT				
DATASET FILE NAME AA0926CP_DS/00A.PRT				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:			MATERIAL/COLOR: BLACK RAL 9005 TEXTURE FINISH	
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XX +/- 0.007		METRIC - MILLIMETER X.X +/- 0.8 X.XX +/- 0.46 X.XX +/- 0.18	ANGLE +/- 1°	
		THIRD ANGLE PROJECTION		
DRAWN BY DACU			DRAWING NUMBER: AA0926CP	
DATE 09/10/14	CHK JPHI	SCALE SCALE:1:5	SHEET 1 OF 1	SIZE B