




PANDUIT P/N	WEIGHT
GM-A0927BL	5 kg (11 lb)

NOTES:
1. IDENTIFICATION: GATEWAY MONITORED ZERO-RU INLINE METER,
(1) 30A IEC60309, 208V / 30A / THREE-PHASE (DELTA)

PART NO. COLOR
GM-A0927BL BLACK RAL 9005

2. ACCESSORY COMPONENTS:
(4) M6 x 12mm MOUNTING SCREWS
(4) M6 x 12mm MOUNTING SCREWS
(4) M6 NUT (CAGED)
(1) M5 NUT (NYLON INSERT)
(1) M5 LOCK WASHER

3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. PHASE (L1, L2, L3) LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. WHEN CONNECTED VIA SERIAL CONNECTION TO GATEWAY, DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE INPUT POWER = 8.6 kW
8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



00A	09/10/14	DACU	JPHI		RELEASED TO PRODUCTION	AA0927CP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGNTHE CLIENT SIGNATUTE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN	
		DATE	
		PRINT	
TITLE SmartZone Gateway-Enabled Zero-RU Inline Meter PN: GM-A0927BL CUSTOMER DRAWING			
ITEM REVISION NAME AA0927CP/00.PRT			
DATASET FILE NAME AA0927CP_DS/00A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR: BLACK RAL 9005 TEXTURE FINISH	
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XX +/- 0.007		METRIC - MILLIMETER X.X +/- 0.8 X.XX +/- 0.46 X.XX +/- 0.18	
ANGLE +/- 1°			
		THIRD ANGLE PROJECTION	
DRAWN BY DACU	DATE 09/10/14	CHK JPHI	SCALE SCALE:1:5
SHEET 1 OF 1		SIZE B	