


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P1N1B1M2M10AKAO	5.6kg (12.3lb)


NOTES:

- IDENTIFICATION: 1RU HORIZONTAL, (10) 5-20R, NETWORKED 120V / 30A / SINGLE PHASE PDU
- ACCESSORY COMPONENTS:
 - (1) QUICK-START GUIDE
 - (4) M6 x 15mm MOUNTING SCREWS
 - (4) #12-24 x 1/2" MOUNTING SCREWS
- PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
- CIRCUIT LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED VIA ETHERNET CONNECTION OR ON-UNIT DISPLAY.
- RoHS COMPLIANT
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- MAXIMUM AVAILABLE INPUT POWER = 2.8 kW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.


PART NO. PIN1B1M2M10AKAO
 COLOR BLACK




FRONT VIEW



REAR VIEW



SIDE VIEW



00A	03/25/14	PJST	MRWA	EDM	RELEASED TO PRODUCTION	12V092BP-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.

THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
 DATE _____
 PRINT _____

TITLE: P1N1B1M2M10AKAO
 CUSTOMER DRAWING

ITEM REVISION NAME: 12V092BP/00
 DATASET FILE NAME: 12V092BP_DC/00A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 INCHES: X.X +/- 0.03, X.XX +/- 0.018, X.XXX +/- 0.007
 METRIC - MILLIMETER: X +/- 0.8, X.X +/- 0.46, X.XX +/- 0.18
 ANGLE: +/- 1°

MATERIAL/COLOR: N/A

DRAWING NUMBER: 12V092BP-DC

THIRD ANGLE PROJECTION

DRAWN BY: PJST, DATE: 03/25/14, CHK: MRWA, SCALE: NONE

SIZE: SHT 1 OF 1, B