

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
V1B2B1M2M24AKA0	7.7kg (17.04lbs)

NOTES:
1. IDENTIFICATION: VERTICAL, (24) NEMA 5-20R, BASIC 120V / 30A / SINGLE-PHASE PDU

PART NO. V1B2B1M2M24AKA0 COLOR BLACK

2. ACCESSORY COMPONENTS:
(1) QUICK-START GUIDE

3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
4. RoHS COMPLIANT.
5. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
6. MAXIMUM AVAILABLE INPUT POWER = 2.8 kW
7. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
8. PRINTED WITH PHASE & CIRCUIT IDENTIFICATION.



PLUG
30 AMP, 125V
TWIST-LOCK
NEMA L5-30P

TWENTY-FOUR (24)
RECEPTACLES
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20R

01A	09-19-14	SAT	MRWA	EDM	RELEASED TO PRODUCTION	12V091TK-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN	
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE	
		PRINT	
TITLE			
BASIC PDU (24) NEMA 5-20R CUSTOMER DRAWING			
ITEM REVISION NAME		12V091TK/01	
DATASET FILE NAME		12V091TK_DC/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007		METRIC - MILLIMETER X. +/- 0.8 X.X +/- 0.46 X.XX +/- 0.18	
ANGLE +/- 1°		N/A	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY SAT		DATE 09-11-14	
CHK MRWA		SCALE 1:8	
SHT 1 OF 1		SIZE B	