THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	WEIGHT
C2CACT5F06SDBI	128 Kg/EACH 282 LBS/EACH
C2CACT5F06SDWI	



NOTES:
1. VISIT OUR ONLINE CATALOG AT WWW.APNDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS [mm]. DIMENSIONS IN PARENTHESES ARE IN INCHES [IN].
3. ACCURATE CABINET PLACEMENT IS ESSENTIAL FOR PROPER ASSEMBLY OF THE AISLE CONTAINMENT SYSTEM. THE FRONT FACE OF THE OPPOSING CABINET FRAMES MUST BE LOCATED 1800mm ±13mm OR 72" ±.5" APART.
4. CONTAINMENT CEILING HEIGHT IS 2110mm - 2244mm [83.1" - 88.3"]
5. DOOR FRAME ALLOWS FOR UP TO 44.45mm [1.75"] OF VERTICAL CABINET ADJUSTMENT.
6. DOOR FRAME STRUCTURE SHIPPED UNASSEMBLED.
7. WINDOWS OF DOORS FRAMES ARE UL94-V0 POLYCARBONATE
8. FOR COLD AISLE APPLICATION, FOR USE WITH:
   - 42 RU NET-ACCESS CABINETS (N*** AND S***)
   - 45 RU NET-ACCESS CABINTES (N*** AND S***)
9. PARTS SUPPLIED (ASSEMBLY REQUIRED):
   (1) DOOR FRAME STRUCTURE
   (2) 640.1mm [25.2"] DOORS
   (1) HARDWARE KIT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/08/12	PJST			RELEASED TO PRODUCTION	12V292AJ

TITLE
NET CONTAIN™ COLD AISLE CONTAINMENT (CAC) DUAL SLIDING DOORS - C2CACT5F06SD
CUSTOMER DRAWING

ITEM REVISION NAME: 12V292AJ/00
DATASET FILE NAME: 12V292AJ_DC/00A

PANDUIT™

MATERIAL: N/A

DRAWING NUMBER: 12V292AJ

DRAWN BY	DATE	CHK	SCALE	SIZE
PJST	10/08/12			A

SHT 1 OF 2

D10100DA/12

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/08/12	PJST			RELEASED TO PRODUCTION	12V292AJ

TITLE

NET CONTAIN™ COLD AISLE CONTAINMENT (CAC) DUAL SLIDING DOORS - C2CACT5F06SD

CUSTOMER DRAWING

ITEM REVISION NAME: 12V292AJ/00

DATASET FILE NAME: 12V292AJ_DC/00A

MATERIAL: N/A

DRAWING NUMBER: 12V292AJ

DRAWN BY	DATE	CHK	SCALE	SIZE
PJST	10/08/12		N/A	A

SHT 2 OF 2

D10100DA/12