

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

|             |                |
|-------------|----------------|
| PANDUIT P/N | WEIGHT         |
| CMRPSV20STL | 13 lb (5.9 kg) |

NOTES:

1. IDENTIFICATION: VERTICAL, (20) 5-20R  
120V / 20A / SINGLE-PHASE POU

|                 |              |
|-----------------|--------------|
| <u>PART NO.</u> | <u>COLOR</u> |
| CMRPSV20STL     | BLACK        |

2. ACCESSORY COMPONENTS:
- (4) #10-32 x 1/2" MOUNTING SCREWS
  - (4) #12-24 x 1/2" MOUNTING SCREWS
  - (2) #10-32 LOCKING COLLAR SCREWS
  - (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. SURGE SUPPRESSION UP TO 330V OR 720 JOULES.


5. UL<sup>®</sup> & c-UL<sup>®</sup> LISTED 1950.

6. RoHS COMPLIANT.


7. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE INPUT POWER = 1.9 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



TOOLLESS MOUNTING  
BUTTON 2X





SURGE ACTIVE LED -


POWER ON LED —

20A THERMAL BREAKER -

- 10 FOOT INLET POWER CORD



PLUG  
20 AMP, 125V, SINGLE-PHASE  
TWIST LOCK  
NEMA L5-20P



TWENTY-FOUR (20)  
RECEPTACLES  
20 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-20R

|     |          |      |      |                        |          |   |   |      |     |     |
|-----|----------|------|------|------------------------|----------|---|---|------|-----|-----|
|     |          |      |      |                        |          |   |   |      |     |     |
|     |          |      |      |                        |          |   |   |      |     |     |
|     |          |      |      |                        |          |   |   |      |     |     |
|     |          |      |      |                        |          |   |   |      |     |     |
|     |          |      |      |                        |          |   |   |      |     |     |
|     |          |      |      |                        |          |   |   |      |     |     |
| 01A | 9-13-12  | PIP  | MRWA | A. ADDED NOTE #9.      | 09V098YN |   |   |      |     |     |
| 00A | 10-26-11 | MRWA | KRKE | RELEASED TO PRODUCTION | 09V098YN |   |   |      |     |     |
| REV | DATE     | BY   | CHK  | DESCRIPTION            | ECN      | - | R | CUST | SUP | OTH |

|                                                                                                                          |  |                                                                                              |  |
|--------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------|--|
| MODEL FILENAME                                                                                                           |  | 09V098YN/01.PRT                                                                              |  |
| CAD FILENAME/LAYERS                                                                                                      |  | 09V098YN_DC/01A.PRT                                                                          |  |
|  PANDUIT CORP TINLEY PARK, ILLINOIS |  |                                                                                              |  |
| VERTICAL, (20) 5-20R<br>POWER OUTLET UNIT<br>CUSTOMER DRAWING                                                            |  |                                                                                              |  |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:<br>INCHES<br>X.X +/- 0.03<br>X.XX +/- 0.015<br>X.XXX +/- 0.005   |  | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN IN<br>INCHES, THIRD ANGLE PROJECTION |  |
| [METRIC - MILLIMETER]<br>X +/- 0.8<br>X.X +/- 0.4<br>X.XX +/- 0.13                                                       |  | ANGLE<br>+/- °                                                                               |  |
| DRAWN BY<br>MRWA                                                                                                         |  | SCALE<br>NONE                                                                                |  |
| DATE<br>10-26-11                                                                                                         |  | DRAWING NO.<br>09V098YN                                                                      |  |
| CHK'D<br>KRKE                                                                                                            |  | DWG<br>B                                                                                     |  |