


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO	WEIGHT
DIRLC7018VP4248	43.09 Kgs/EA 95 LBS/EA

NOTES:

- VISIT OUR ONLINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- PRIMARY DIMENSIONS ARE IN MILLIMETERS (mm). DIMENSIONS IN PARENTHESES ARE IN INCHES (IN).
- INLET DUCT TO BE USED WITH CISCO 7018 SWITCH.



E-RAIL DEPTH MUST BE 657.76mm
25.896in

TITLE
INLET DUCT W/42-48RU AIR DAMS ON RIGHT SIDE ONLY
FOR CISCO 7018 SWITCH
IN 1000mm WIDE N-TYPE CABINET (DIRLC7018VP4248)
CUSTOMER DRAWING

ITEM REVISION NAME
12V360AN/00

DATASET FILE NAME
12V360AN_DC/00A

PANDUITTM

MATERIAL:
N/A



DRAWING NUMBER:
12V360AN

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	10/07/2013	TGO			RELEASED	12V360AN


DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2	SIZE
TGO	10/07/2013		N/A		A

D10100DA/12

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



E-RAIL DEPTH MUST BE 657.76mm
25.896in



TITLE					INLET DUCT W/42-48RU AIR DAMS ON RIGHT SIDE ONLY FOR CISCO 7018 SWITCH IN 1000mm WIDE N-TYPE CABINET (DIRLC7018VP4248) CUSTOMER DRAWING				
ITEM REVISION NAME					12V360AN/00				
DATASET FILE NAME					12V360AN_DC/00A				
									
					MATERIAL: N/A				
					DRAWING NUMBER: 12V360AN				
DRAWN BY	DATE	CHK	SCALE						
TGO	10/07/2013		N/A	SHT 2 OF 2					
									SIZE A

D10100DA/12