

NOTES:
1. IDENTIFICATION: 2RU HORIZONTAL, (6) L6-20R, METERED
208V / 20A / SINGLE-PHASE POU


2. ACCESSORY COMPONENTS:
(4) 10-32 x 1/2" MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS

4. POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).

6. RoHS COMPLIANT.


8. MAXIMUM AVAILABLE INPUT POWER = 3.3 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



SIX (6)
RECEPTACLES
20 AMP, 250V
TWIST LOCK
NEMA L6-20R

01A	9-5-12	PIP	MRWA	A. UPDATED NOTE #5 & 8. B. ADDED NOTE #9.	09V098CC				
00A	2-24-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098CC				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098CC/01.PRT	
CAD FILENAME/LAYERS		09V098CC_DC/01A.PRT	
			
2RU HORIZONTAL, (6) L6-20R, METERED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ANGLE	
X.X +/- 0.03	X.X +/- 0.8	ALL DIMENSIONS ARE GIVEN IN	
X.XX +/- 0.015	X.XX +/- 0.4	INCHES, THIRD ANGLE PROJECTION	
X.XXX +/- 0.005	X.XX +/- 0.13		
DRAWN BY MAV	MAT'L:	SCALE NONE	
DATE 2-24-11		DRAWING NO. 09V098CC	DWG B
CHK'D KRKE			SIZE