

NOTES:
1. IDENTIFICATION: 1RU HORIZONTAL, MIXED (4) C-13 & (4) C-19
208V / 30A / SINGLE-PHASE POU




2. ACCESSORY COMPONENTS:
(4) 10-32 x 1/2" MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS

4. POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).

6. RoHS COMPLIANT.

8. MAXIMUM AVAILABLE INPUT POWER = 5 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



MODEL FILENAME		09V098DY/01.PRT	
CAD FILENAME/LAYERS		09V098DY_DC/01A.PRT	
			
1RU HORIZONTAL, MIXED (4) C-13 & (4) C-19 POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- 1°		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 2-24-11		DRAWING NO. 09V098DY	
CHK'D KRKE		DWG B	