




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. NOTES:



DETAIL A  
(SCALE 4X)



REAR VIEW




FRONT VIEW


—LED

20 AMP, SINGLE POLE UL LISTED ELECTRO  
MECHANICAL SWITCH/BREAKER  
(2 PLACES)



NETWORKED ETHERNET CONNECTION  
(SEE DETAIL A)



PLUG (2)  
30 AMP, 125V  
TWIST-LOCK  
NEMA L5-30P



TEN (10)  
RECEPTACLES  
20 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-20R

							TITLE 1RU HORIZONTAL, (10) 5-20R, MONITORED AUTO-TRANSFER SWITCH POWER OUTLET UNIT CUSTOMER DRAWING					
							ITEM REVISION NAME 09V098VM/01.PRT					
							DATASET FILE NAME 09V098VM_DC/01A.PRT					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES    +/- 0.03    METRIC - MILLIMETER    X.    +/- 0.8    ANGLE X.XX    +/- 0.018    X.X    +/- 0.46    +/- 1° X.XXX    +/- 0.007    X.XX    +/- 0.18					
01A	4-8-13	MRWA	KRKE		A. CORRECTED DRAWING NUMBER IN TITLE BLOCK    B. UPDATED NOTE 1 C. CORRECTED VOLTAGE IN PLUG FIELD	09V098VM	 THIRD ANGLE PROJECTION					
00A	1-25-13	MRWA	KRKE		RELEASED TO PRODUCTION	09V098VM	DRAWING NUMBER: 09V098VM					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MRWA	DATE 1-25-13	CHK KRKE	SCALE NONE	SHT 1 OF 1	SIZE B