




2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO.	WEIGHT
PEHF2	6.7 LBS. [3.0 Kg]

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN PARENTHESES ARE METRIC (mm).
- PARTS SUPPLIED:
 - 1- PEHF CARRIAGE ASSEMBLY
 - 1- PEHF DOOR ASSEMBLY
 - 1- PACK OF 4 SCREWS
 - 1- INSTRUCTION SHEET



07A	11-26-13	BAME	FGR	CMK	UPDATED VIEWS	10V134AB-DC
06B	6-10-13	BAME	FGR	CMK	REVISED AND REDRAWN; PREVIOUS REVS OMITTED REVISED TITLE BLOCK	10V134AB-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					
(PEHF2) PATCHRUNNER HIGH CAPACITY HORIZONTAL CABLE MANAGER					
CUSTOMER DRAWING					
ITEM REVISION NAME					
10V134AB/07					
DATASET FILE NAME			MATERIAL:		
10V134AB_DC/07A					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			N/A		
.X ± .XX ±					
			DRAWING NUMBER:		
THIRD ANGLE PROJECTION					
DRAWN BY			10V134AB-DC		
PM					
DATE			SIZE		
1-17-11					
CHK			SHT 1 OF 1		
SRK					
SCALE			A		
NONE					

2

1

D10100DA/15