


1




NOTES:



1. IDENTIFICATION: HORIZONTAL, (10) 5-20R NETWORKED
& ENVIRONMENTAL MONITORED
120V / 20A / SINGLE-PHASE POU

<u>PART NO.</u>	<u>COLOR</u>
PN1A1C0BA10E1	BLACK

2. ACCESSORY COMPONENTS:
(4) #10-32 x 1/2" MOUNTING SCREWS
(4) #12-24 x 1/2" MOUNTING SCREWS
3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. POWER (A,V,PF,KWH) MONITORING AND ENVIRONMENTAL
SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET
CONNECTION, LOCAL DISPLAY, OR OPTIONAL REMOTE DISPLAY
(PVQ-RD).
5. UL® & c-UL® LISTED 60950.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR
A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE
WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 1.9 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE
NATIONAL, STATE, AND LOCAL CODES.



ADJUSTABLE MOUNTING BRACKETS



01A	8-27-12	PIP	MRWA	B. REVISED DETAIL A.	09V098JA				
00B	3-1-12	MRWA	KRKE	A. ADJUSTED OVERLAY POSITION	09V098JA				
00A	11-22-11	MRWA	KRKE	RELEASED TO PRODUCTION	09V098JA				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098JA/01.PRT	
CAD FILENAME/LAYERS		09V098JA_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, (10) 5-20R NETWORKED & ENVIRONMENTAL MONITORED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: METRIC - MILLIMETER X.X +/- 0.6 X.XX +/- 0.4 X.XXX +/- 0.13		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MRWA		SCALE NONE	
DATE 11-22-11		DRAWING NO. 09V098JA	
CHK'D KRKE		DWG  SIZE	