


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DETAIL A
(SCALE 4X)

PANDUIT P/N	WEIGHT
QN1D2B2BN30P1	17 lb (7.7 kg)

NOTES:

1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED & ENVIRONMENTAL MONITORED 230V / 32A / SINGLE-PHASE POU

PART NO. QN1D2B2BN30P1
COLOR BLACK

2. ACCESSORY COMPONENTS:
 (4) M6 x 20mm MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. POWER (A,V,PF,KWH) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION, LOCAL DISPLAY, OR OPTIONAL REMOTE DISPLAY (PVQ-RD).

5. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE MARKED.


6. RoHS COMPLIANT.

7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.


8. MAXIMUM AVAILABLE INPUT POWER = 7.4 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.


TOOLLESS MOUNTING
BUTTON 2X



TOOLLESS MOUNTING BUTTON LOCATION




NETWORKED ETHERNET CONNECTION
(SEE DETAIL A)



3 METER INLET POWER CORD

16 AMP, 2 POLE UL LISTED ELECTRO MECHANICAL SWITCH/BREAKER
2 PLACES



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01A	8-29-12	PIP	MRWA	A. UPDATED DETAIL A. B. ADDED BUTTON MOUNTING NOTE.	09V098KH				
00A	11-22-11	MRWA	KRKE	RELEASED TO PRODUCTION	09V098KH				

MODEL FILENAME	09V098KH/01.PRT	
CAD FILENAME/LAYERS	09V098KH_DC/01A.PRT	
PANDUIT CORP. TINLEY PARK, ILLINOIS		
VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED & ENVIRONMENTAL MONITORED POWER OUTLET UNIT CUSTOMER DRAWING		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
INCHES	±0.03	[METRIC - MILLIMETER] ANGLE
X.X	±0.03	X.X ±0.8
X.XX	±0.015	X.X ±0.4
X.XXX	±0.005	X.XX ±0.13
DRAWN BY	MRWA	MAT'L:
DATE	11-22-11	SCALE
CHK'D	KRKE	NONE
DRAWING NO.		DWG
09V098KH		B
		SIZE