



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



KNOCK-OUT FOR  
PDU POWER CORD

FRONT  
PERFORATED  
SINGLE HINGE  
DOOR

SPLIT SIDE  
PANEL



INTEGRAL  
CABINET TOP  
CABLE ROUTING  
SYSTEM

SPLIT SIDE  
PANEL

REAR  
PERFORATED  
SPLIT  
DOORS

1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. RAIL ADJUSTMENT MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL. INDEPENDENT ADJUSTABLE REAR EQUIPMENT MOUNTING RAILS (EIA) ADJUST FROM 141mm [5.5in] TO 437mm [17.2in] AND FROM 526mm [20.7in] TO 933mm [36.7in] WITH PDU BRACKETS AND CABLE MANAGEMENT FINGERS IN PLACE.
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS 15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in], 15.88mm [.625in], 15.88mm [.625in], 12.7mm [.5in]...ETC.
6. PARTS SUPPLIED:
  - BASE CABINET
  - FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)
  - REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)
  - SPLIT SIDE PANELS (SEE CHART ON SHEET 2)
  - EQUIPMENT RAILS FRONT & REAR (SEE CHART ON SHEET 2)
  - PDU BRACKETS (SEE CHART ON SHEET 2)
  - CABINET HARDWARE KIT
  - INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING. 1360 Kg (3000 LBS)
10. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
11. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
12. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.
13. MAXIMUM EQUIPMENT DEPTH, 959mm [37.75].

# TITLE

NET-ACCESS S-TYPE CABINET W/INTEGRAL  
CABINET TOP CABLE ROUTING SYSTEM - NO  
CASTERS 700mm WIDE X 1070mm DEEP FAMILY  
CUSTOMER DRAWING

# ITEM REVISION NAME

12V352CC/01.PRT

# DATASET FILE NAME

12V352CC\_DC/01A.PRT


**PANDUIT**

# MATERIAL:

N/A

# DRAWING NUMBER:

12V352CC-DC



THIRD ANGLE  
PROJECTION

# DRAWN BY

PBS

# DATE

7-07-14

# CHK

ROJC

# SCALE

NONE

SHT 1 OF 5

# SIZE

A



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	11-24-14	MDCA	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX
00A	7-07-14	PBS	ROJC	TCN	RELEASED TO PRODUCTION	12V352CC-DC

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	FRONT CAGE NUT E-RAIL	REAR CAGE NUT FINGER MGMT E-RAIL	REAR CAGE NUT VERTICAL PATCH E-RAIL	STANDARD FDJ BRACKETS	CASTERS	CABLE MGMT FINGERS	VERTICAL PATCHING	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S7212*T9	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	01	01	02	02	02	00	02	00	00	00	134 Kg/EACH 296 LBS/EACH	155 Kg/EACH 341 LBS/EACH
S7512*T9	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	01	01	02	02	02	00	02	00	00	00	141 Kg/EACH 311 LBS/EACH	161 Kg/EACH 356 LBS/EACH
S7812*T9	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	01	01	02	02	02	00	02	00	00	00	148 Kg/EACH 326 LBS/EACH	168 Kg/EACH 371 LBS/EACH
S7219*T9	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	01	01	00	02	02	00	02	00	00	00	101 Kg/EACH 223 LBS/EACH	122 Kg/EACH 268 LBS/EACH
S7519*T9	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	01	01	00	02	02	00	02	00	00	00	108 Kg/EACH 238 LBS/EACH	128 Kg/EACH 283 LBS/EACH
S7819*T9	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	01	01	00	02	02	00	02	00	00	00	115 Kg/EACH 253 LBS/EACH	135 Kg/EACH 298 LBS/EACH

\* DENOTES COLOR

"B" = BLACK


"W" = WHITE

							TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM - NO CASTERS 700mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V352CC/01.PRT					
							DATASET FILE NAME 12V352CC_DC/01A.PRT					
01A	11-24-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX						
00A	7-07-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CC-DC	 THIRD ANGLE PROJECTION				DRAWING NUMBER: 12V352CC-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY PBS	DATE 7-07-14	CHK ROJC	SCALE NONE	SHT 2 OF 5	SIZE A

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



A


A

							TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM - NO CASTERS 700mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING						
							ITEM REVISION NAME 12V352CC/01.PRT						
							DATASET FILE NAME 12V352CC_DC/01A.PRT						
01A	11-24-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX							
00A	7-07-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CC-DC	 THIRD ANGLE PROJECTION						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY PBS	DATE 7-07-14	CHK ROJC	SCALE NONE	MATERIAL:  N/A	DRAWING NUMBER: 12V352CC-DC	SIZE A

2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



(6) LOCATIONS TAPPED FOR M10 THREADED ROD

REAR

(1) 165mm X 165mm  
[6.5in] [6.5in]  
KNOCKOUT FOR PDU  
POWER CORDS  
COMPATIBLE  
W/COOL BOOT  
P/N: CTGN6X6



(12) CABLE OPENINGS  
(83mm X 120mm)  
[3.26in] [4.7in]  
WITH BEZELS  
AND COVERS  
COMPATIBLE  
W/ COOL BOOT  
P/N: CTGN3X5


FRONT  
TOP VIEW

FRONT DOOR, REAR DOOR,  
AND SIDE PANELS NOT SHOWN

01A	11-24-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00A	7-07-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CC-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM - NO CASTERS 700mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING	
ITEM REVISION NAME 12V352CC/01.PRT	
DATASET FILE NAME 12V352CC_DC/01A.PRT	
MATERIAL:  N/A	
DRAWING NUMBER: 12V352CC-DC	
DRAWN BY PBS	DATE 7-07-14
CHK ROJC	SCALE NONE
SHT 4 OF 5	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



01A	11-24-14	MDCA	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX
00A	7-07-14	PBS	ROJC	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	12V352CC-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE NET-ACCESS S-TYPE CABINET W/INTEGRAL CABINET TOP CABLE ROUTING SYSTEM - NO CASTERS 700mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING	
ITEM REVISION NAME 12V352CC/01.PRT	<b>PANDUIT</b>
DATASET FILE NAME 12V352CC_DC/01A.PRT	
MATERIAL:  N/A	DRAWING NUMBER: 12V352CC-DC
THIRD ANGLE PROJECTION	
DRAWN BY PBS	DATE 7-07-14
CHK ROJC	SCALE NONE
SHT 5 OF 5	SIZE A