





NOTES:
1. IDENTIFICATION: VERTICAL, (24) 6-20R
208V / 30A / THREE-PHASE WYE POU

<u>PART NO.</u>	<u>COLOR</u>
VB0B1P3BN24H1	BLACK

2. ACCESSORY COMPONENTS:

- (4) #10-32 x 1/2" MOUNTING SCREWS
- (4) #12-24 x 1/2" MOUNTING SCREWS
- (2) #10-32 LOCKING COLLAR SCREWS
- (2) L-BRACKETS

- TOOLLESS MOUNTING
BUTTON 2X



MODEL FILENAME		09V098EP/01.PRT	
CAD FILENAME/LAYERS		09V098EP_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, (24) 6-20R POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ANGLE	
X.X +/- 0.03	X +/- 0.8	ALL DIMENSIONS ARE GIVEN IN	
X.XX +/- 0.015	X.X +/- 0.4	INCHES, THIRD ANGLE PROJECTION	
X.XXX +/- 0.005	X.XX +/- 0.13		
DRAWN BY	MAT'L:	SCALE	
MAV		NONE	
DATE		DRAWING NO.	DWG
10-15-10		09V098EP	B
CHK'D			SIZE
KRKE			