

NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19
230V / 16A / SINGLE-PHASE

PANDUIT P/N	WEIGHT
VB0D2A0BA30P1	14.1 lb (6.4 kg)

2. ACCESSORY COMPONENTS:
(4) M6 x 20mm MOUNTING SCREWS
(4) #12-24 x 1/2" MOUNTING SCREWS
(2) #10-32 LOCKING COLLAR SCREWS
(2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, GOST, AND IS CE MARKED.

5. RoHS COMPLIANT.

6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.


7. MAXIMUM AVAILABLE INPUT POWER = 3.7 KW

8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.


A diagram of a rectangular box with a horizontal dimension line below it. The dimension line is labeled "64.75 (1644.7)".

TOOLLESS MOUNTING BUTTON LOCATION


66.25 (1682.8)




— 3 METER INLET POWER CORD



PLUG
16 AMP, 250V, SINGLE-PHASE
2P/3W
IEC 60309, SPLASHPROOF



TWENTY-FOUR (24)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

01A	8-30-12	PIP	MRWA	A. UPDATED NOTE #7. B. ADDED NOTE #8.	09V098NL					
00A	2-10-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098NL					
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH

MODEL FILENAME		09V098NL/01.PRT	
CAD FILENAME/LAYERS		09V098NL_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (6) C-19, METERED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- °		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 2-10-11		DRAWING NO. 09V098NL	
CHK'D KRKE		DWG B	