


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
VB0D2B4CM48M1	24 lb (10.9 kg)



NOTES:

1. IDENTIFICATION: VERTICAL, (48) C-13
230V / 32A / SINGLE-PHASE POU

<u>PART NO.</u>	<u>COLOR</u>
VB0D2B4CM48M1	BLACK

2. ACCESSORY COMPONENTS:
- (4) M6 x 20mm MOUNTING SCREWS
 - (4) 12-24 x 1/2" MOUNTING SCREWS
 - (2) #10-32 LOCKING COLLAR SCREWS
 - (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).




4. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE & C-TICK MARKED.

5. RoHS COMPLIANT.


6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

7. MAXIMUM AVAILABLE INPUT POWER = 7.4 KW

8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES



PLUG (2)
32 AMP, 250V, SINGLE-PHASE
2P/3W
IEC 60309, SPLASHPROOF



FOURTY-EIGHT (48)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

01A	8-15-12	PIP	MRWA	D. ADDED BUTTON MOUNTING NOTE.	09V098GV				
00B	10-19-11	MRWA	KRKE	C. UPDATED OUTLET TYPE IN MAIN TITLE BLOCK A. UPDATED NOTES 2, 4, & 7 B. ADDED NOTE 8	09V098GV				
00A	2-10-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098GV				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098GV/01.PRT	
CAD FILENAME/LAYERS		09V098GV_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, (48) C-13 POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		ANGLE +/-	
DRAWN BY MAV		SCALE NONE	
DATE 2-10-11		DRAWING NO. 09V098GV	
CHK'D KRKE		DWG B	