

NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19, METERED
230/400V / 32A / THREE-PHASE WYE POU

<u>PART NO.</u>	<u>COLOR</u>
VB1D2P3BN30P1	BLACK

2. ACCESSORY COMPONENTS:

- (4) M6 x 20mm MOUNTING SCREWS
- (4) #12-24 x 1/2" MOUNTING SCREWS
- (2) #10-32 LOCKING COLLAR SCREWS
- (2) L-BRACKETS

4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1).

6. RoHS COMPLIANT.

8. MAXIMUM AVAILABLE INPUT POWER = 22.1 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

