




SIMPLEX FIBER OPTIC SC TO SC PATCH CORD							
PANDUIT PART NO.	CABLE				SC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR
F5S3-3M*Y	RISER (OFNR)	50/125um OM2	SIMPLEX 3.0mm	ORANGE	0.30dB	20dB	ELECTRIC IVORY
F6S3-3M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	ELECTRIC IVORY
F9S3-3M*Y		9/125um OS1		YELLOW	0.75dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										SIMPLEX FIBER OPTIC PATCH CORD SC TO SC CONFIGURATION CUSTOMER DRAWING				
											 TINLEY PARK, ILL 60477			
											 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (.3) (.XX) ± .03 (.8) ANGLES		DRAWING FILENAME M02779CG_DC_00A.prt
												SCALE NONE		
												DRAWN BY MC	REVIEW DRAWING NUMBERS	PART NO. SEE TABLE
R	06-04-07	MC		RELEASED TO PRODUCTION	02779-37					DATE 05-23-07	DRAWING NO. 02779-37 (SHT. 2 of 2)		SIZE A	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D				

