


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT VIEW

SHOWN W/O DUSTCAPS




PORT DESIGNATIONS


AS VIEWED FROM THE FRONT
WITH ADAPTERS REMOVED FOR CLARITY

PANDUIT P/N	DESCRIPTION
FCX0-12-3Y	OPTIMIZED 50/125 10GbE MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FCX-12-3Y	50/125 10GbE MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FCZ0-12-3Y	OPTIMIZED 50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FCZ-12-3Y	50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FC5-12-3Y	50/125 MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FC6-12-3Y	62.5/125 MULTIMODE 12 FIBER, MTP TO SC CASSETTE MODULE
FC9-12-3Y	9/125 SINGLEMODE 12 FIBER, MTP TO SC CASSETTE MODULE

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
 - a. MODULE MATERIAL: PLASTIC
 - b. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 5.28oz [149.8g]
5. DIMENSIONS IN BRACKETS ARE METRIC.



										FIBER OPTIC CASSETTE MODULE 12 FIBER, MTP TO DUPLEX SC CONFIGURATION CUSTOMER DRAWING	
											PANDUIT TM CORP. TINLEY PARK, ILL 60477
											ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (.0.3) (.XX) ± .03 (.0.8) ANGLES
										DRAWING FILENAME M02068AK_DC/00G	SCALE NONE
										DRAWN BY MC	REVIEW DRAWING NUMBERS
										DATE 12-10-04	PART NO. SEE TABLE
										DRAWING NO. 02068-39	SIZE A
02	09-16-09	EFK		RELEASED TO PRODUCTION	02068-39						
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	OTH	CHK'D MTV	