







PANDUIT PART NUMBER	WEIGHT
FR1VRA6X4	1.22 LB/EACH 555g/EACH

△C

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 6x4 INSIDE VERTICAL RIGHT ANGLE FITTING IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. THE FIBERRUNNER 6x4 INSIDE VERTICAL RIGHT ANGLE FITTING INCLUDES:
ONE (1) INSIDE VERTICAL RIGHT ANGLE BASE,
ONE (1) FIXED COVER SECTION,
ONE (1) MOVEABLE COVER SECTION
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38778BK_DC_FR1VRA6X4_01.prt

CAD_FILENAME/LAYERS

FR1 VRA6X4.pdf

PANDUIT

CORP TINLEY PARK, ILLINOIS

FIBERRUNNER 6x4 INSIDE VERTICAL RIGHT ANGLE FITTING (FRIVRA6X4)

 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X)	±	(.XXX)	±
(.XX)	±.03	(.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY MSO

DATE	8-17-04
------	---------

CHK'D	SMF
-------	-----

	MAT'L:
--	--------

ABS

SCALE	NONE
-------	------

DRAWING NO.

38778 - 11

DWG
A
SIZE

-	-----	---	--	D. ADDED DIMENSION C. REVISED GENERAL NOTES	-----	--	--		
1	7-6-06	DTP	RN	B. REVISED PART WEIGHT A. REVISED DRAWING TITLE	38778-11	RN	RN		
R	8-17-04	MSO	SMF	RELEASED TO PRODUCTION	38778-11	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH