THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:
1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-13			

FIBER OPTIC PATCH CORD
DUPLEX ST TO ST CONFIGURATION
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY: MC
DATE: 04-27-07
CHK'D:
REVIEW DRAWING NUMBERS

DRAWING FILENAME: M02779BE_DC_00A.prt
SCALE: NONE
PART NO.: SEE TABLE, SHT. 2
DRAWING NO.: 02779-13 (SHT. 1 of 2)
SIZE: A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX ST TO ST FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				ST CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	COLOR
FXD2-2M*Y	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH
F5D2-2M*Y		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH
F6D2-2M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH
F9D2-2M*Y		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH
FXPD2-2M*	PLENUM (OFNP)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH
F5PD2-2M*		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH
F6PD2-2M*		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH
F9PD2-2M*		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH
FXLD2-2M*	LOW SMOKE ZERO HALOGEN (LSZH) IEC	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH
F5LD2-2M*		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH
F6LD2-2M*		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH
F9LD2-2M*		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-13			

FIBER OPTIC PATCH CORD
DUPLEX ST TO ST CONFIGURATION
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY: MC
DATE: 04-27-07
CHK'D:
REVIEW DRAWING NUMBERS

DRAWING FILENAME: M02779BE_DC_00A.prt
SCALE: NONE
PART NO.: SEE TABLE
DRAWING NO.: 02779-13 (SHT. 2 of 2)
SIZE: A