


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX OPTI-PLUG KEYED "Q" TO SC FIBER OPTIC PATCH CORD										
PANDUIT PART NO.	CABLE				OPTI-PLUG KEYED "Q"			SC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	COLOR
FXD6PQ-3M*Y	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	WHITE	0.30dB	26dB	ELECTRIC IVORY
F5D6PQ-3M*Y		50/125um OM2		ORANGE	0.30dB	20dB	WHITE	0.30dB	20dB	ELECTRIC IVORY
F6D6PQ-3M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	WHITE	0.30dB	20dB	ELECTRIC IVORY

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										DUPLEX FIBER OPTIC PATCH CORD OPTI-PLUG KEYED "O" TO SC CONNECTOR CONFIGURATION CUSTOMER DRAWING
										 PANDUITTM CORP. TINLEY PARK, ILL 60477
										 THIRD ANGLE PROJECTION
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
										DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES
										SCALE NONE
										PART NO. SEE TABLE
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-20					DRAWING NO. 02779-20 (SHT. 2 OF 2)
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	CHK'D	SIZE A