






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SIMPLEX FIBER OPTIC SC TO LC PATCH CORD

PANDUIT PART NO.	CABLE				SC CONNECTOR			LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR	MAX. IL	RL	COLOR
FXF3-10M*Y	RISER (OFNR)	10GbE 50/125um OM3	SIMPLEX 1.6mm	AQUA	0.30dB	26dB	ELECTRIC IVORY	0.30dB	26dB	ELECTRIC IVORY
F6F3-10M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	ELECTRIC IVORY
F9F3-10M*Y		9/125um OS1		YELLOW	0.75dB	55dB	BLUE	0.35dB	55dB	BLUE

\* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

											SIMPLEX FIBER OPTIC PATCH CORD SC TO LC CONFIGURATION CUSTOMER DRAWING		
												 <div>TINLEY PARK, ILL 60477</div>	
											 <div>THIRD ANGLE PROJECTION</div>	<div>ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.</div> <div>DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES</div>	
											DRAWING FILENAME M02779CH_DC_00A.prt		
											SCALE NONE		
											PART NO. SEE TABLE		
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-38						DRAWING NO. 02779-38 (SHT. 2 of 2)		SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	OTH	CHK'D			