




NOTES:
1. IDENTIFICATION: 1RU HORIZONTAL, (10) C-13
208V / 30A / SINGLE-PHASE POU

2. NECESSARY COMPONENTS:
 - (4) 10-32 x 1/2" MOUNTING SCREWS
 - (4) 12-24 x 1/2" MOUNTING SCREWS
3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. UL® & c-UL® LISTED 1950.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE POWER = 5 KW

PANDUIT P/N	WEIGHT
HB0B1L4BT10M1	6 lb (2.7 kg)



PLUG
30 AMP, 250V, SINGLE-PHASE
TWIST LOCK
NEMA L6-30P



TEN (10)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

00A	2-24-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098DG				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098DG/00.PRT	
CAD FILENAME/LAYERS		09V098DG_DC/00A.PRT	
			
1RU HORIZONTAL, (10) C-13 POWER OUTLET UNIT (HB0B1L4BT10M1) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		ANGLE +/- °	
DRAWN BY MAV		SCALE NONE	
DATE 2-24-11		DRAWING NO. 09V098DG	
CHK'D KRKE		DWG B SIZE	