




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PLUG
63 AMP, 250V, SINGLE-PHASE
2P/3W
IEC 60309, SPLASHPROOF



SIX (9)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

00A	2-10-11	MAV	KRKE	RELEASED TO PRODUCTION	09V098GU				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

NOTES:

1. IDENTIFICATION: 1RU, (9) C-19 HORIZONTAL
230V / 48A / SINGLE-PHASE POU


<u>PART NO.</u>	<u>COLOR</u>
HB0D2C3BN09N1	BLACK

2. ACCESSORY COMPONENTS:
(4) 10-32 x 1/2" MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. UNIT COMPLIES WITH IEC 60950-1, EN55022, EN55024, AND IS CE MARKED.
5. RoHS COMPLIANT.
6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
7. MAXIMUM AVAILABLE POWER = 11 KW

PANDUIT P/N	WEIGHT
HB0D2C3BN09N1	15 lb (6.8 kg)



MODEL FILENAME		09V098GU/00.PRT	
CAD FILENAME/LAYERS		09V098GU_DC/00A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU, (9) C-19 HORIZONTAL POWER OUTLET UNIT (HB0D2C3BN09N1) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005 [METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 2-10-11		DRAWING NO. 09V098GU	
CHK'D KRKE		DWG B SIZE	