





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT	FERRULE TYPE
NKMOP**	.098 LB/10 PCS. (44.5 G/10 PCS.)	ZIRCONIA (CERAMIC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. FJ DUPLEX PLUG ACCEPTS HIGH PERFORMANCE 62.5/125 MICRON AND 50/125 MICRON MULTIMODE GLASS OPTICAL FIBER CABLE.
3. DESIGNED FOR SIMPLE FIELD TERMINATION.
4. THE MAXIMUM INSERTION LOSS PER CONNECTOR IS .35 dB.
5. OPERATING TEMPERATURE RANGE IS FROM -40° TO +70° C.
6. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED IN TIA/EIA-568-B3.
7. DIMENSIONS IN PARENTHESES ARE IN METRIC.

DRAWING FILENAME M01302CK_DC_00A.prt		SIZE A
NETKEY FIBER OPTIC CONNECTOR MULTIMODE FJ DUPLEX PLUG (NKMOP**) CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	
	PRODUCT SPEC	
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) .2 (.XXX) .010 (.XX) .02 ANGLES 1°	
	SCALE NONE	
DRAWN BY MC	REVIEW DRAWING NUMBERS	
DATE 03-12-02	PART NO. NKMOP**	
CHK'D	DRAWING NO. 01302-37	

R	03-12-02	MC		RELEASED TO PRODUCTION	01302-37				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH