


NOTES:

1. BRAIDED STRAP IS #4 AWG STRANDED COPPER, TIN PLATED FERRULES ARE TIN PLATED COPPER.
2. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
3. PARTS ARE UL LISTED AND CSA CERTIFIED FOR BONDING APPLICATIONS ONLY.



PANDUIT PART NUMBER	BRAIDED STRAP SIZE	INSULATION	NO. OF BRAIDS IN FERRULE	DIMENSIONS - IN [mm]							
				L	D	S	W	C	T	H DIA	FERRULE LENGTH
BS201246EU	4 AWG	NO	1	12.00 [304.8]	10.75 [273.1]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]
BS201846EU	4 AWG	NO	1	18.00 [457.2]	16.75 [425.5]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]
BS202446EU	4 AWG	NO	1	24.00 [609.6]	22.75 [577.9]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]

								PANDUIT CORP. TINLEY PARK, ILLINOIS					
								TWO-HOLE BRAIDED BONDING STRAPS CUSTOMER DRAWING					
05	6/11	JHNU	JHNU	REVISED TONGUE MARKINGS: cULus WAS UL				N11002BF-C41745	RGB	RGB	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION		
04	2/09	JHNU	JHNU	REMOVED CSA SYMBOL FROM DRAWING									
03	1/09	JHNU	JHNU	REMOVED AMPERE RATING FROM TABLE							UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		
02	1/09	JHNU	JHNU	REVISED NOTES ADDED FERRULE INFORMATION TO TABLE									
01	10/08	JHNU	DWDA	REVISED NOTE 1: #4 AWG WAS #6, REMOVED NOTE 2							DRAWN BY JHNU	MAT'L:	
00	2/08	JHNU	DWDA	DRAWING RELEASED							DATE 2/08	SCALE NONE	
REV	DATE	BY	CHK	DESCRIPTION				ECN	-R	SUP	CHK'D	DRAWING NO / CAD FILE C41745_05	DWG B SIZE