

Compact All-In-One NVR Appliance

The CIRRUS CR47 compact video server (NVR) has been designed for performance and peace of mind. Offering recording capacity up to 6TB, the CR47 offers key features such Quick Setup Wizard, high performance INTEL processor, dedicated SSD boot drive (OS) and dual Gigabit Ethernet.



Base Specifications

Processor	Intel® Core i7-4790T
Memory	8GB DDR3
Operating System	Windows Embedded 7
Drive Bays	1 x 3.5"
Drive Capacities	1TB, 2TB, 3TB, 4TB, 6TB
Drive Interface	SATA
Boot Drive (OS)	128GB SSD SATA3
Video Outputs	HDMI, DP, VGA
Max. Resolution	4096 x 2160 (4K Ultra HD)
Power Supply	External 12~24VDC (84W)
Networking	2 x GbE LAN
Accessories	DP to DVI Cable 12VDC Power Supply (84W)
Form Factor	2U Compact Chassis
Dimensions	11.8" (W) x 2.6" (H) x 10.7" (D)
Operating Temp.	0°C - 60°C (32°F - 140°F)
Warranty	2 Years
Compliance	CE, FCC

Available Options

19" Rack Mount Kit	3 Year Warranty Upgrade
--------------------	-------------------------

Features

- Intel® Core i7 Series Processor
- Up to 120 Mbps Recording Throughput
- Up to 6 TB Internal Storage
- Designed for 24/7 Video Recording
- Dedicated SSD Boot Drive
- Low Noise Compact Design
- Pre-loaded VMS Software

Built tough, built to last.

High performance solid state boot drive, internal realtime hardware and software watchdogs and fully recoverable operating system image extends the reliability of your critical installations.

Quick Setup Wizard

The CR47 is delivered with our unique Quick Setup Wizard, pre-loaded and ready to go. It allows you to apply network and other settings, at first boot, and select which VMS software solution to deploy on your NVR appliance.

