

# CIRRUS CR5-4U24

recording

## 4U 24-Bay Enterprise Video Server

The CIRRUS CR5-4U24 NVR enterprise video server has been designed for performance and peace of mind. Offering recording capacity up to 144TB, the CR5-4U24 offer key features such Quick Setup Wizard, configurable RAID levels, redundant power, SSD boot and dual Gigabit Ethernet.



### Base Specifications

<b>Processor</b>	Intel® Xeon® E5-2620v3
<b>Memory</b>	16GB DDR4 2133MHz
<b>Operating System</b>	Windows Embedded 7
<b>Drive Bays</b>	24 x 3.5" (Hot-Swappable)
<b>Drive Capacities</b>	1TB, 2TB, 3TB, 4TB, 5TB, 6TB
<b>Drive Interface</b>	SATA or SAS
<b>Max. Raw Storage</b>	144TB
<b>Hardware RAID</b>	0,1,5,6,10,50,60
<b>Boot Drive</b>	128GB SSD SATA3
<b>Dedicated Graphics</b>	GeForce 210 1024MB DDR3
<b>Video Outputs</b>	HDMI, DVI, VGA
<b>Max. Resolution</b>	2560 x 1600
<b>Power Supply</b>	100-240V, 740W, Redundant
<b>AC Input Frequency</b>	50 ~ 60 Hz
<b>Networking</b>	2 x GbE + 1 x IPMI LAN
<b>Accessories</b>	USB Keyboard & Mouse
<b>Form Factor</b>	4U Rack, 25.5" Depth
<b>Dimensions</b>	7" x 17.2" x 26"
<b>Operating Temp.</b>	10°C - 35°C (50°F - 95°F)
<b>Operating Humidity</b>	8% - 90% (non-condensing)
<b>Warranty</b>	3 Years On Site NBD 8/5
<b>Compliance</b>	FCC, CE

### Features

- Intel® Xeon® E5 Series Processor
- Up to 600 Mbps Recording Throughput
- Up to 144 TB (Configurable RAID)
- Designed for 24/7 Video Recording
- Dedicated Graphics Card
- Redundant Power Supply
- Pre-loaded VMS Software

### Quick Setup Wizard

The CR5-4U24 is delivered with our unique Quick Setup Wizard, pre-loaded and ready to go. It allows you to apply network and other settings, at first boot, and select which VMS software solution to deploy on your NVR appliance.



**IONODES**