

Ultra-Compact All-In-One NVR Appliance

The CIRRUS CR40 ultra compact video server (NVR) has been designed for performance and peace of mind. Offering recording capacity up to 1TB, the CR40 offers key features such Quick Setup Wizard, high performance INTEL processor, dedicated SSD boot drive (OS) and Gigabit Ethernet.



Base Specifications

Processor	Intel® Core i3-6100U
Memory	4GB DDR4
Operating System	Windows Embedded 7
Drive Bays	1 x 2.5"
Drive Capacities	1TB
Drive Interface	SATA
Boot Drive (OS)	128GB SSD SATA3
Video Outputs	HDMI, miniDP
Max. Resolution	4096 x 2304 (4K Ultra HD)
Audio	7.1 audio (HDMI, miniDP) Audio in/out (front jack)
USB Ports	4 x USB 3.0
Expansion	1 x SD card slot
Power Supply	External 12~19VDC (65W)
Networking	1 x GbE LAN WIFI (802.11ac) + Bluetooth
Accessories	19VDC Power Supply (65W) VESA Mounting Kit
Dimensions	4.5" (W) x 1.9" (H) x 4.4" (D)
Operating Temp.	0°C - 50°C (32°F - 122°F)
Warranty	3 Years
Compliance	CE, FCC

Features

- Intel® Core i3 Series Processor
- Intel® Dual Band Wireless
- Dual-Purpose Recording & Live Viewing
- Dedicated 128GB SSD Boot Drive
- 1TB Internal Storage
- Designed for 24/7 Video Recording
- Ultra Compact Design

Built tough, built to last.

High performance solid state boot drive, internal realtime hardware and software watchdogs and fully recoverable operating system image extends the reliability of your critical installations.

Quick Setup Wizard

The CR40 is delivered with our unique Quick Setup Wizard, pre-loaded and ready to go. It allows you to apply network and other settings, at first boot, and select which VMS software solution to deploy on your NVR appliance.

