



107713596 | M14AS-270  
**Angled Flush Mounted Faceplate, gray**

## General Specifications

Color	Gray
Mount Type	Flush
Product Type	Flush mount faceplate
Total Ports, quantity	4
Package Quantity	25

## Dimensions

Depth	13.46 mm   0.53 in
Height	121.92 mm   4.80 in
Width	78.74 mm   3.10 in

## Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

## Environmental Specifications

Safety Standard	UL
-----------------	----

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system