



108333048 | M12LE-215
LE Type Flush Mounted Faceplate, two port cream
• Available for use with the DYMO® labeling solution

General Specifications

Color	Cream
Mount Type	Flush
Product Type	Flush mount modular faceplate
Total Ports, quantity	2
Application	Used with M-Series modular information outlet
Package Quantity	1

Dimensions

Depth	8.38 mm 0.33 in
Height	122.17 mm 4.81 in
Width	72.14 mm 2.84 in
Weight	0.04 kg 0.10 lb

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system