



108333147 | M14LE-215

## LE Type Flush Mounted Faceplate, four port cream

- Available for use with the DYMO® labeling solution

### General Specifications

Color	Cream
Mount Type	Flush
Product Type	Flush mount modular faceplate
Total Ports, quantity	4
Application	Used with M-Series modular information outlet
Package Quantity	1

### Dimensions

Depth	8.38 mm   0.33 in
Height	122.17 mm   4.81 in
Width	72.14 mm   2.84 in
Weight	0.04 kg   0.09 lb

### Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

### Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system