



108333154 | M14LE-246

LE Type Flush Mounted Faceplate, four port ivory

- Available for use with the DYMO® labeling solution

General Specifications

| | |
|-----------------------|---|
| Color | Ivory |
| Mount Type | Flush |
| Product Type | Flush mount modular faceplate |
| Total Ports, quantity | 4 |
| Application | Used with M-Series modular information outlet |
| Package Quantity | 1 |

Dimensions

| | |
|--------|---------------------|
| Depth | 8.38 mm 0.33 in |
| Height | 122.17 mm 4.81 in |
| Width | 72.14 mm 2.84 in |
| Weight | 0.04 kg 0.08 lb |

Mechanical Specifications

| | |
|---------------|--|
| Material Type | High-impact, flame retardant, UL-rated 94 V-0, thermoplastic |
|---------------|--|

Environmental Specifications

| | |
|-----------------|----------|
| Safety Standard | cUL UL |
|-----------------|----------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |