



108564675 | M13CLS-246

**Flexible Faceplate with Single Gang Frame, ivory**

- Available for use with the DYMO® labeling solution

## General Specifications

Color	Ivory
Mount Type	Flush
Product Type	Designer furniture faceplate
Total Ports, quantity	3
Application	Flush mounted triplex modular faceplates designed to fit modular furniture raceway covers
Package Quantity	1

## Dimensions

Compatible Knockout Height	35.05 mm   1.38 in
Compatible Knockout Tolerance	±.01 in
Compatible Knockout Width	68.83 mm   2.71 in
Depth	7.37 mm   0.29 in
Height	46.74 mm   1.84 in
Width	79.50 mm   3.13 in
Weight	0.02 kg   0.05 lb

## Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

## Environmental Specifications

Safety Standard	cUL   UL
-----------------	----------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system