



108685017 | M28L-246

L Type Flush Mounted Double Gang Faceplate, eight port, ivory

- Available for use with the DYMO® labeling solution

General Specifications

Color	Ivory
Mount Type	Flush
Product Type	Flush mount modular faceplate
Total Ports, quantity	8
Application	Used with M-Series modular information outlet
Package Quantity	1

Dimensions

Depth	7.37 mm 0.29 in
Height	115.82 mm 4.56 in
Width	117.09 mm 4.61 in
Weight	0.06 kg 0.12 lb

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Environmental Specifications

Safety Standard	cUL UL
-----------------	----------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system