



700011125 | D-181781
6-to-1 Unit Splitter, for outdoor cable diameter of 0.41 in

Construction Materials

Material Type, body ABS plastic

Dimensions

Height 8.13 mm | 0.32 in
Length 50.80 mm | 2.00 in
Width 20.32 mm | 0.80 in

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Product Type Unit splitter kit
Color Black
Compatible Interface LC | LC, keyed | SC | ST
Includes Six unit splitter | Split tube seal | Syringe
Ordering Note Order B sealant separately
Package Quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2011/65/EU | Compliant |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

