



760034199 | SFC-LCR-09-BL

**Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, single-mode**

## Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1   OS2)
Ferrule Geometry	Pre-radiused
Ferrule Material	Zirconia

## Dimensions

Compatible Cable Diameter	0.9 mm   0.0 in
Length	32.00 mm   1.26 in

## General Specifications

Interface	LC
Body Style	BTW
Interface Feature	Standard
Color	Blue
Package Quantity	1

## Mechanical Specifications

Cable Retention Strength, maximum	0.45 kg @ 0 ° 1.00 lb @ 0 °
-----------------------------------	--------------------------------

## Optical Performance

Insertion Loss, typical	0.20 dB
Return Loss, minimum	55.0 dB
Insertion Loss Change, mating	0.30 dB
Insertion Loss Change, temperature	0.30 dB

## Optical Specifications

Optical Components Standard	ANSI/TIA-568-C.3
-----------------------------	------------------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

760034199 | SFC-LCR-09-BL

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)