

760117887 | MFC-LCF-09-5X

LazrSPEED® Fiber Qwik II-LC Connector™, field installable, aqua



This product will be discontinued on: June 30, 2016

Construction Materials

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber (OM2+) LazrSPEED® 300, 50 µm multimode fiber (OM3) LazrSPEED® 550, 50 µm multimode fiber (OM4)
Ferrule Geometry	Factory polished
Ferrule Material	Zirconia

Dimensions

Compatible Cable Diameter	0.9 mm 0.0 in
Length	42.60 mm 1.68 in

General Specifications

Interface	LC
Body Style	BTW
Interface Feature	Field Installable Mechanical splice
Color	Aqua
Package Quantity	1

Mechanical Specifications

Cable Retention Strength, maximum	0.45 kg @ 0 ° 1.00 lb @ 0 °
-----------------------------------	--------------------------------

Optical Performance

Insertion Loss, typical	0.27 dB
Return Loss, minimum	20.0 dB
Insertion Loss Change, mating	0.20 dB
Insertion Loss Change, temperature	0.30 dB

Optical Specifications

Optical Components Standard	ANSI/TIA-568-C.3
-----------------------------	------------------

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications



760117887 | MFC-LCF-09-5X

RoHS 2011/65/EU Compliant
ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss Change, mating Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)