



760157800 | OVRHDRACK

3 in (76 mm) Channel x 9.4 in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (4U) 3/8 Sq Punch, Black

Dimensions

| | |
|-----------------------|--------------------|
| Channel Width | 3.0 in |
| Depth | 76.2 mm 3.0 in |
| Dimensional Standards | EIA-310-E |
| Height | 238.8 mm 9.4 in |
| Width | 500.4 mm 19.7 in |

General Specifications

| | |
|------------------|--|
| Product Type | Mini-rack, overhead |
| Rack Units | 4 |
| Color | Black |
| Finish | Powder-coated, textured |
| Includes | Instruction sheet Six 5/16-18 hex nuts Six 5/16-18 hex screws Sixteen M6 cage nuts Sixteen M6 mounting screws Two flat washers Two ladder clamp brackets Two mounting brackets |
| Package Quantity | 1 |
| Packaging Type | Assembled |
| Rack Type | EIA 19 in |

Mechanical Specifications

| | |
|--------------------|-------------------|
| Material Type | Steel |
| Static Load Rating | 27.2 kg 60.0 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2011/65/EU | Compliant |
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

