



760158592 | OVRHDRACKVCM

3 in (76 mm) Channel x 9.4in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (4U) 3/8 Sq Punch, Black, with mini VCM

Dimensions

Channel Width	3.0 in
Depth	264.2 mm 10.4 in
Dimensional Standards	EIA-310-E
Height	238.8 mm 9.4 in
Weight	3.64 kg 8.02 lb
Width	596.9 mm 23.5 in

General Specifications

Product Type	Mini-rack, overhead
Rack Units	4
Color	Black
Finish	Powder-coated, textured
Includes	Instruction sheet Mini vertical cable management, with cover Six 5/16-18 hex nuts Six 5/16-18 hex screws Sixteen M6 cage nuts Sixteen M6 mounting screws Three 1/4-20 hex screws Three flat washers Two flat washers Two ladder clamp brackets Two mounting brackets
Package Quantity	1
Packaging Type	Assembled
Rack Type	EIA 19 in

Mechanical Specifications

Material Type	Steel
Static Load Rating	27.2 kg 60.0 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

