



760173849 | TUBE-RD-88-1M-YL
SpeedPRO™ Round Convoluted Tube for Drop Solutions, 88 mm OD, 1 m, yellow

Dimensions

System Dimensions	100 mm x 100 mm 220 mm x 100 mm 300 mm x 100 mm 4 in x 4 in 8 in x 4 in 12 in x 4 in
Length	1000.0 mm 39.4 in
Tube Outer Diameter	88.00 mm 3.46 in
Width	88.0 mm 3.5 in
Weight	1.05 kg 2.31 lb

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Safety Standard	UL

General Specifications

Color	Yellow
Product Type	Convoluted tube
Brand	SpeedPRO™
Includes	Convoluted tube
Minimum Order Quantity	1
Package Quantity	1
Product Feature	Round
Warranty	20 years

Mechanical Specifications

Material Type	High density polyethylene (HDPE)
---------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

