



760187195 | 360-E-MOD-2U-48
360 Evolve 48-port flat panel

Dimensions

Depth	43.18 mm 1.70 in
Depth, with cable management	6.80 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	88.90 mm 3.50 in
Weight	1.04 kg 2.30 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	5e 6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Total Ports, quantity	48
Cable Type	U/UTP (unshielded)
Product Type	Panel
Brand	SYSTIMAX 360™ SYSTIMAX®
Color	Cool gray
Label Height	0.43 in
Label Length	1.33 in
Modules, quantity	48
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	2

Mechanical Specifications

Panel Style	Straight
-------------	----------

Product Specifications



760187195 | 360-E-MOD-2U-48

Material Type
Wiring

High-impact, flame retardant, thermoplastic | Powder-coated steel
T568A | T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification