

760187203 | 360-E-ANG-MOD-1U-24
360 Evolve 24-port angled panel



Dimensions

| | |
|-----------------------------------|----------------------|
| Depth | 139.70 mm 5.50 in |
| Depth, with cable management | 10.60 in |
| Diameter Over Dielectric, maximum | 1.168 mm 0.046 in |
| Diameter Over Dielectric, minimum | 0.762 mm 0.030 in |
| Height | 44.45 mm 1.75 in |
| Weight | 0.59 kg 1.30 lb |
| Width | 482.60 mm 19.00 in |

Electrical Specifications

| | |
|---|--------------------------------|
| ANSI/TIA Category | 5e 6 6A |
| Current Rating | 1.5 A @ 20 °C 1.5 A @ 68 °F |
| Dielectric Withstand Voltage, RMS, conductive surface | 1500 Vac @ 60 Hz |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1000 Vac @ 60 Hz |
| Insulation Resistance, minimum | 500 MOhm |

Environmental Specifications

| | |
|-----------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Safety Standard | cUL UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|-----------------------|---------------------------|
| Total Ports, quantity | 24 |
| Cable Type | U/UTP (unshielded) |
| Product Type | Panel |
| Brand | SYSTIMAX 360™ SYSTIMAX® |
| Color | Cool gray |
| Label Height | 0.43 in |
| Label Length | 1.33 in |
| Modules, quantity | 24 |
| Package Quantity | 1 |
| Rack Type | EIA 19 in |
| Rack Units | 1 |

Mechanical Specifications

| | |
|-------------|--------|
| Panel Style | Angled |
|-------------|--------|

Product Specifications



760187203 | 360E-ANG-MOD-1U-24

Material Type
Wiring

High-impact, flame retardant, thermoplastic | Powder-coated steel
T568A | T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification