



106664139 | M30MC-246
Rectangular Mounting Collar, ivory

General Specifications

| | |
|-----------------------|--------------------------------|
| Color | Ivory |
| Mount Type | Snap-in |
| Product Type | Mounting collar |
| Total Ports, quantity | 1 |
| Application | Fit into a rectangular opening |
| Package Quantity | 100 |

Dimensions

| | | | |
|--------|----------|--|---------|
| Depth | 11.68 mm | | 0.46 in |
| Height | 25.40 mm | | 1.00 in |
| Width | 26.16 mm | | 1.03 in |
| Weight | 0.00 kg | | 0.01 lb |

Mechanical Specifications

| | |
|---------------|--|
| Material Type | High-impact, flame retardant, UL-rated 94 V-0, thermoplastic |
|---------------|--|

Environmental Specifications

| | |
|-----------------|----------|
| Safety Standard | cUL UL |
|-----------------|----------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |