



106837222 | M81-246 BLANK  
**Blank Coaxial Adapter, ivory**

## General Specifications

Product Type	Multimedia blank
Color	Ivory
Mount Type	Snap-in
Package Quantity	1

## Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
---------------	---

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

