



107059917 | 110AW2-300
110 Wiring Blocks, 300 pair count, without 110 connecting blocks

Dimensions

Depth	82.55 mm 3.25 in
Height	274.07 mm 10.79 in
Width	272.29 mm 10.72 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL

General Specifications

Product Design	110
Product Type	Block
Color	White
Package Quantity	1
Pairs, quantity	300

Mechanical Specifications

Block Type	A
Material Type	Copper alloy High-impact, flame retardant, thermoplastic
Plug Insertion Life, minimum	200 times

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

